


SH1-QU

Sleek and Unique:

- Antimicrobial for pathogen build up resistance*¹.
- Wipe Down with common Healthcare cleaners.
- Integrated cable reduces connection issues.
- Scan all the common barcode types.
- Smooth Surface / Reduced Crevices.
- Light weight for reduced fatigue.
- High ROI with high durability.
- Unique, crevice-free trigger.
- 1 Year Warranty.



Flat and uneven shape*²

A flat shape is achieved by eliminating the trigger switch and adopting a touch switch. It can be sterilized with alcohol and has a smooth body that is easy to wipe and clean.



Compact design

Small and thin scanner. Ideal for long hours of work and space-saving operations. It is convenient to carry and can be used anywhere.




Soundless confirmation

Since reading can be confirmed by vibration and LED without emitting sound, it can be used safely even in a quiet hospital room.



Inventory & Pharmacy



Bedside Care




Mobile Workstation

Scanner Specifications	
Model Number	SH1-QU
Scanner	
Method	Area Sensor
Readable 2D Codes	QR Code, Micro QR Code, SQRC, DataMatrix (ECC200), PDF417, MicroPDF417, Maxi code, Aztec, GS1 DataBar Composite (EAN.UCC Composite)
Readable 1D Barcodes	EAN-13/8 (JAN-13/8), UPC-A/E, UPC/EAN (with add-on), Interleaved 2 of 5 (ITF), Standard 2 of 5 (STF), CODABAR (NW-7), CODE39, CODE93, CODE128, GS1-128 (EAN-128), GS1 DataBar (RSS)
Minimum resolution 2D Codes	0.167mm
Minimum resolution 1D Barcodes	0.125mm
PCS	0.3 or more
Angle	±50°
Scanning Confirmation	LED blue, Vibrator and Buzzer
Communication	
Method	USB keyboard and USB-COM interfaces
Connector	USB connector (A type)
Cable	1.5m straight cable
Power	
Power supply	Supplied from connection ³
Operating environment	
Humidity	10 to 90% RH (non-condensing)
Operating temperature	-5 to 50°C (23 to 122°F)
Illumination	0 to 10,000 lx (fluorescent lamp in daytime)
Drop Test ⁴	1.5m on concrete x 30 times
Physical Characteristics	
Weight (excluding cable)	Approx. 55g

1. JISz2801/ISO22196
 2. Only body. Excluding cable.
 3. This type of connection may not be possible depending on the model of the PC or USB hub.
 4. Results obtained in test at room temperature; not meant as a guarantee.
 ** Product appearance and specifications are subject to change without notice.

Dimensions Unit: mm (for reference only)



Contents

- Scanner with cable
- Operation guide
- Instruction manual [HP↓](#)

Software

- Keyboard interface software (QR_kbif) [HP↓](#)
- USB driver (Active USB-COM port driver) [HP↓](#)
- Scanner Setting 2D [HP↓](#)
- SQRC Setting [HP↓](#)

[HP↓](#) Item with this symbol can be downloaded free of charge from www.denso-adc.com

INVENTOR OF



THE QR CODE®